



Double-ended ring spanner set, straight, Number of keys: 11



Order data

Order number	617610 11
GTIN	4018754085224
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw widths.

STAHLWILLE – With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Thin, flat rings for use in restricted places. With **AS Drive** profile.

Standard:

DIN 837 B / ISO 3318

Material:

STAHLWILLE – Chrome alloy steel; non-flaking chrome-plated over nickel; smoothed finish surface.

Content:

1 each double-ended ring spanner No. 617600 / 617950: 6×7; 8×9; 10×11; 12×13; 14×15; 16×17; 18×19; 20×22; 21×24; 27×32; 30×34

Technical description

Number of keys	11
Width across flats	metric
Type of product	Spanner

Accessories

Double-ended ring spanner, straight Width across flats 20X22 mm	617600 20X22
Double-ended ring spanner, straight Width across flats 12X13 mm	617600 12X13
Double-ended ring spanner, straight Width across flats 6X7 mm	617600 6X7
Double-ended ring spanner, straight Width across flats 16X17 mm	617600 16X17
Double-ended ring spanner, straight Width across flats 30X34 mm	617600 30X34
Double-ended ring spanner, straight Width across flats 21X24 mm	617600 21X24
Double-ended ring spanner, straight Width across flats 10X11 mm	617600 10X11
Double-ended ring spanner, straight Width across flats 14X15 mm	617600 14X15
Double-ended ring spanner, straight Width across flats 18X19 mm	617600 18X19
Double-ended ring spanner, straight Width across flats 27X32 mm	617600 27X32
Double-ended ring spanner, straight Width across flats 8X9 mm	617600 8X9