



Double-ended ring spanner, shallow cranked, Width across flats: 10X11 mm



Order data

Order number	616500 10X11
GTIN	4018754021673
Item class	63A

Description

Version:

Drop-forged. With close tolerance jaw widths. Thin, flat rings for use in restricted places. With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Shallow cranked head at each end. With **AS-Drive** profile.

Standard:

DIN 897 / ISO 3318

Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish.

Technical description

Width across flats 1	10 mm
Width across flats 2	11 mm
Spanner length L	188 mm
maximum ring height $h_{1\max}$	9.5 mm
maximum ring $\varnothing D_1 \max$	14.6 mm
maximum ring $\varnothing D_2 \max$	15.9 mm
Width across flats	metric
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chromium-plated over nickel
Type of product	Spanner

