



Torque screwdriver with scale, maximum torque: 600cNm



Order data

Order number	659933 600
GTIN	4013288101730
Item class	63F

Description

Version:

Kraftform handle for easy transmission of the required torque. With **Rapidaptor** quick-change holder for 1/4 inch bits with C 6.3 **and** E 6.3 shank.

Torque setting by hand using a micrometer scale (from size 600 using the integral auxiliary tool or a 17AF open spanner). With pistol grip for delivering high torques.

Function:

When the set torque is reached the screwdriver triggers, with clearly audible and perceptible signals. The triggering torque is unrestricted.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Rapidaptor free-running coupling shank available from our eShop (No. 675035 size 6.3F).

Technical description

Scale graduation, 1 graduation =	25 cNm
Display	analogue
maximum torque	600 cNm

Torque measuring accuracy	±6 %
Bit socket	F 6.3
Bit socket	D 6,3
Torque range	300 - 600 cNm
Torque range	3 - 6 Nm
Standard	DIN EN ISO 6789
Measurement process	Torque
Setting the trigger value	with adjustment scale
Feedback	triggering
Overall length L	150 mm
Connection format	Bit holder 1/4 inch
Reversible reading	cNm
Weight	122 g
Adjustable trigger value	adjustable
Trigger principle	mechanical short-travel release
Calibration	O1
Direction of tightening	Right-hand tightening
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Measurement technology	mechanical
Release signalling	akustisk
Release signalling	haptisk
Manufacturer's designation	7400 pistol
Type of product	Torque screwdriver

Services

Calibration Torque screwdriver maximum torque 0,04-20 N·m

020200 0,04-20

