



## Double-ended ring spanner, straight, Width across flats: 6X7mm



### Order data

Order number	617600 6X7
GTIN	4018754021222
Item class	63A

### Description

#### Version:

Drop-forged. With close tolerance jaw widths.

**STAHLWILLE** – With easy-grip fluted shaft. Optimum flexional resistance, good torque transmission. Thin, flat rings for use in restricted places. With **AS-Drive** profile.

#### Standard:

**DIN 837 B / ISO 3318**

#### Material:

**STAHLWILLE** – Chrome alloy steel; non-flaking chrome-plated over nickel; smoothed finish surface.

### Technical description

maximum ring $\varnothing D_1$ max	10.5 mm
Width across flats 1	6 mm
maximum ring height $h_{1\ max}$	4.5 mm
maximum ring $\varnothing D_2$ max	12 mm
Spanner length L	100 mm
Width across flats 2	7 mm
Width across flats	metric
Ring setting	0 degrees
Manufacturing process	drop forged
Material	Chrome alloy steel
Surface	chrome-plated (non-flaking)

Type of product

Spanner