


HOLEX®**Ideal snips with 2-component handles, left-hand, overall length: 260 mm**

Order data

Order number	766041 260
GTIN	4045197166944
Item class	72D

Description

Version:

Cutter head drop forged, blades induction hardened. Adjustable pivot pins, double leverage with integrated return spring.

Ultra-fine serrated. Snip jaws made of **stainless steel** (HRC 58 – 60), handles of steel plate, nickel plated. 2-component handle with non-slip insert of soft material, easy on the hand.

Cutting capacity: Sheet metal up to 1.8 mm, stainless steel up to 1.2 mm.

Application:

For continuous straight and shaped cutting.

Length cutter: 33 mm

Technical description

overall length	260 mm
Length cutter	33 mm
Application type	left-hand