

Garant
HSS jobber drill W, uncoated, Ø DC h8: 6,3mm

Order data

| | |
|--------------|---------------|
| Order number | 114200 6,3 |
| GTIN | 4045197015716 |
| Item class | 11B |

Description
Version:

Standard core without core taper.
Precision ground point.
Ground flute with high helix.
Bright ground surface finish.
With point geometry shape A from size 2.0 mm.

Recommendation:
Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c$$

Technical description

| | |
|---|--------------|
| Nominal Ø D _c | 6.3 mm |
| Number of cutting edges Z | 2 |
| Flute length L _c | 63 mm |
| Tolerance nominal Ø | h8 |
| Shank Ø D _s | 6.3 mm |
| Overall length L | 101 mm |
| Feed f in long-chipping aluminium plastics | 0.14 mm/rev. |
| Standard | DIN 338 |
| recommended maximum drilling depth L ₂ | 53.6 mm |
| Point angle | 130 degrees |
| Shank | Plain shank |

| | |
|-----------------|---------------|
| Coating | uncoated |
| Tool material | HSS |
| Type | W |
| Helix angle | 35-40 degrees |
| Through-coolant | no |
| Colour ring | yellow |
| Type of product | Jobber drill |

User data

| | Suitability | V_c | ISO code |
|----------------------------|---|----------|----------|
| Alu plastics | suitable | 70 m/min | N |
| Aluminium (short chipping) | suitable | 45 m/min | N |
| Alu > 10% Si | suitable only under restricted conditions | 40 m/min | N |
| Oil | suitable | | |
| wet maximum | suitable | | |