



Double-ended ring spanner, straight, phosphated, Width across flats: 8X9 mm



Order data

Order number	617900 8X9
GTIN	4045197385666
Item class	62A

Description

Version:

Drop-forged. With close tolerance jaw widths.

HOLEX – With oval shaft.

Standard:

DIN 837 B / ISO 3318

Material:

HOLEX – Chrome vanadium steel, phosphated.

Spanner length L: 115 mm

maximum ring $\varnothing D_1$ max: 13.5 mm

maximum ring $\varnothing D_2$ max: 15 mm

maximum ring height $h_{1\max}$: 5.5 mm

Technical description

maximum ring height $h_{1\max}$	5.5 mm
Width across flats 2	9 mm
Spanner length L	115 mm
maximum ring $\varnothing D_2$ max	15 mm
maximum ring $\varnothing D_1$ max	13.5 mm
Width across flats 1	8 mm
Width across flats	metric
Ring setting	0 degrees

Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	phosphated
Product name attribute	phosphated
Type of product	Spanner