

Erdi**Ideal snips, right-hand cutting, overall length: 240mm**

Order data

Order number	766100 240
GTIN	4010220010969
Item class	73X

Description

Version:

Drop-forged head, blades induction hardened. Adjustable pivot pins, double leverage with integrated return spring.

Ultra-fine serrated. Snip jaws made of high quality **stainless steel S** (HRC 60 – 62), forged solid steel non-slip handles.

Cutting capacity: Metal sheets up to 2.0 mm, stainless steel sheets up to 1.5 mm.

- **Improved sheet metal clearance due to optimised cutting chamfer.**
- **Reduced opening angle of the handles and blade extension back to the pivot means less effort is required during cutting.**

Application:

For continuous straight and shaped cutting.

Technical description

overall length	240 mm
Length cutter	24 mm
Application type	right-hand cutting
Type of product	Scissors

Accessories

Repair kit for Ideal snips

766110