



Torque screwdriver set, maximum torque: 250cNm



Order data

Order number	659938 250
GTIN	3148516763693
Item class	63V

Description

Version:

Robust torque screwdriver, adjustable with parallax-free micrometer scale. 1/4 inch internal square at the end of the handle.

Function:

When the set torque is reached the screwdriver triggers and signals clearly (audibly and perceptibly). It is then again immediately ready for use.

Standard:

Geprüft nach DIN EN ISO 6789.

Content:

9 bits assorted: 1 pc. each of: PZ 1-2-3; hexagon 3-4-5 mm; slot-head 4.5-6.5-8

Ratchet handle: No. 659937

Bit extension: 100 mm

Torque screwdriver No. 659936: 1 pc. size 250

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

maximum torque	250 cNm
Calibration	O1

Release signalling	acoustic
Square drive	1/4 in
Torque measuring accuracy	±6 %
Measurement technology	mechanical
Test certificate	Manufacturer's test certificate
Direction of tightening	Right-hand tightening
Reversible reading	Nm
Data can be recorded	no
Connection format	Bit holder 1/4 inch
Adjustable trigger value	adjustable
Trigger principle	mechanical slip clutch
Feedback	triggering
Setting the trigger value	with adjustment scale
Display	analogue
Measurement process	Torque
Standard	ISO 6789
Bit socket	D 6,3
Type of product	Torque screwdriver

Services

CalibrationTorque screwdriver maximum torque 0,04-20 N·m	020200 0,04-20
--	----------------

Accessories

Torque screwdriver with scale maximum torque 250 cNm	659936 250
Torque screwdriver with scale maximum torque 1000 cNm	659936 1000
Handle with reversible ratchet	659937