



Torque screwdriver iTorque® with digital display, maximum torque: 150cNm



Order data

Order number	659935 150
GTIN	4010995368869
Item class	63K

Description

Version:

High-quality comfortable metal-plastic composite handle ensures ergonomic working and easy application of the set torques. Quick and easy reading and setting **via the large digital display**. Automatic switch-off after 15 seconds (battery life at least 1 year). The battery can be changed at the factory or during recalibration. Display changeover between Nm and lbf in. Includes bit-holder blade No. 659932 to take 1/4 inch bits.

Units of measure: Nm, lbf in

Advantage:

An **integral counter function** records the number of tightening operations, providing the basis for monitoring by test instruments.

Function:

On reaching the set torque value, the screwdriver can be felt and heard to trigger and is then again immediately ready for use.

Application:

For controlled tightening of screws to a pre-set torque.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

For further options see No. 659940 - 659946.

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Resolution	1 cNm
------------	-------

Ø	34 mm
Display	digital
maximum torque	150 cNm
Torque measuring accuracy	±6 %
Bit socket	D 6,3
Bit socket	F 6.3
Torque range	40 - 150 cNm
Torque range	0.4 - 1.5 Nm
Number of batteries contained	1
Measurement process	Torque
Standard	DIN EN ISO 6789
Setting the trigger value	digital, adjustable
Trigger principle	mechanical short-travel release
Weight	322 g
Overall length L	134 mm
Reversible reading	Nm
Reversible reading	lbf·in
Connection format	exchangeable blade
Feedback	triggering
Adjustable trigger value	adjustable
Series	iTorque®
Calibration	O1
Direction of tightening	Right-hand tightening
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Release signalling	akustisk
Release signalling	haptisk
Measurement technology	mechanical
Power supply	Battery-powered

Battery type	CR1220 MFR FH
chemical composition	Lithium
Manufacturer's designation	iTorque®
Torque fixed setting	no
Type of product	Torque screwdriver

Services

CalibrationTorque screwdriver maximum torque 0,04-20 N·m	020200 0,04-20
--	----------------

Accessories

Torque interchangeable bladefor Phillips Cross-head size 1	659940 1
Torque interchangeable bladePozidriv Cross-head size 1	659941 1
Torque interchangeable bladefor Phillips Cross-head size 0	659940 0
Bit-holder	659932
Torque interchangeable bladePozidriv Cross-head size 0	659941 0