



Torque screwdriver set, maximum torque: 1000cNm



Order data

Order number	659938 1000
GTIN	3148516763853
Item class	63V

Description

Version:

Robust torque screwdriver, adjustable with parallax-free micrometer scale. 1/4 inch internal square at the end of the handle.

Function:

When the set torque is reached the screwdriver triggers and signals clearly (audibly and perceptibly). It is then again immediately ready for use.

Standard:

Geprüft nach DIN EN ISO 6789.

Content:

9 bits assorted: 1 pc. each of: PZ 1-2-3; hexagon 3-4-5 mm; slot-head 4.5-6.5-8

Ratchet handle: No. 659937

Bit extension: 100 mm

Torque screwdriver No. 659936: 1 pc. size 1000

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

maximum torque	1000 cNm
Calibration	O1

Square drive	1/4 in
Release signalling	acoustic
Test certificate	Manufacturer's test certificate
Measurement technology	mechanical
Torque measuring accuracy	±6 %
Direction of tightening	Right-hand tightening
Adjustable trigger value	adjustable
Reversible reading	Nm
Connection format	Bit holder 1/4 inch
Data can be recorded	no
Feedback	triggering
Trigger principle	mechanical slip clutch
Setting the trigger value	with adjustment scale
Measurement process	Torque
Display	analogue
Standard	ISO 6789
Bit socket	D 6,3
Type of product	Torque screwdriver

Services

CalibrationTorque screwdriver maximum torque 0,04-20 N·m	020200 0,04-20
--	----------------

Accessories

Torque screwdriver with scale maximum torque 1000 cNm	659936 1000
Handle with reversible ratchet	659937
Torque screwdriver with scale maximum torque 250 cNm	659936 250