

KANON**Torque screwdriver with scale, maximum torque: 300cNm****Order data**

| | |
|--------------|---------------|
| Order number | 659949 300 |
| GTIN | 4580125347564 |
| Item class | 66F |

Description**Version:**

Setting using a micrometer scale. Profiled light alloy handle.

Function:

When the set torque is reached the screwdriver triggers and signals clearly (audibly and perceptibly). It is then again immediately ready for use.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

| | |
|----------------------------------|--------------|
| Display | analogue |
| Ø | 34 mm |
| maximum torque | 300 cNm |
| Scale graduation, 1 graduation = | 1 cNm |
| Torque measuring accuracy | ±6 % |
| Bit socket | F 6.3 |
| Torque range | 40 - 300 cNm |
| Torque range | 0.4 - 3 Nm |
| Feedback | triggering |

| | |
|---------------------------|-------------------------------------|
| Connection format | Bit holder 1/4 inch |
| Adjustable trigger value | adjustable |
| Reversible reading | cNm |
| Overall length L | 157 mm |
| Standard | DIN EN ISO 6789 |
| Trigger principle | mechanical short-travel release |
| Setting the trigger value | with adjustment scale |
| Measurement process | Torque |
| Weight | 214 g |
| Calibration | O3 |
| Direction of tightening | For right- and left-hand tightening |
| Test certificate | Manufacturer's test certificate |
| Data can be recorded | no |
| Measurement technology | mechanical |
| Release signalling | akustisk |
| Release signalling | haptisk |
| Type of product | Torque screwdriver |

Services

| | |
|---|------------------|
| CalibrationTorque screwdrivers, clockwise / anti-clockwise maximum torque 0,04-20/2 N·m | 020260 0,04-20/2 |
|---|------------------|