



## Double-ended crescent ring spanner, Jaw widths: 19X22mm



### Order data

Order number	618000 19X22
GTIN	4018754022090
Item class	63A

### Description

#### Version:

Drop forged ring spanner in a crescent shape. Close tolerance jaw widths. Torsion-resistant fluted shaft. With **AS Drive** profile.

#### Application:

Specially for working on engine blocks, e.g. fitting carburettors, alternators etc. and everywhere where nuts and bolts are difficult to reach using normal ring spanners.

#### Material:

Chrome alloy steel, non-flaking chrome-plated over nickel; smoothed finish surface (no sharp edges).

### Technical description

Ring $\varnothing D_2$	32 mm
Wrench length	225 mm
Width across flats 1	19 mm
Width across flats 2	22 mm
Ring $\varnothing D_1$	28 mm
Width across flats	metric
Head height h	9 mm
Manufacturing process	drop forged
Material	Chrome alloy steel

Surface	chrome-plated (non-flaking)
Ring end AS drive	yes
Crescent shape	yes
Type of product	Spanner