



HSS jobber drill N, uncoated, Ø DC h8: 38mm



Order data

Order number	116320 38
GTIN	4045197029928
Item class	12C

Description

Version:

Special surface treatment, resulting in reduced tendency to edge build-up **and improved chip evacuation.**

Recommendation:

Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c.$$

Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530.**

Technical description

Flute length L_c	200 mm
Nominal $\varnothing D_c$	38 mm
Feed f in steel $< 750 \text{ N/mm}^2$	0.25 mm/rev.
Number of cutting edges Z	2
Tolerance nominal \varnothing	h8
Overall length L	349 mm
Morse taper MT size	4
Standard	DIN 345
recommended maximum drilling depth L_2	143 mm
Point angle	118 degrees
Shank	Morse taper

Coating	uncoated
Tool material	HSS
Type	N
Helix angle	20-30 degrees
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	40 m/min	P
Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	25 m/min	P
GG(G)	suitable only under restricted conditions	25 m/min	K
Oil	suitable		
wet maximum	suitable		