

KANON
Torque screwdriver with scale, maximum torque: 500cNm

Order data

Order number	659949 500
GTIN	4580125347571
Item class	66F

Description
Version:

Setting using a micrometer scale. Profiled light alloy handle.

Function:

When the set torque is reached the screwdriver triggers and signals clearly (audibly and perceptibly). It is then again immediately ready for use.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Display	analogue
Ø	40 mm
maximum torque	500 cNm
Scale graduation, 1 graduation =	2.5 cNm
Torque measuring accuracy	±6 %
Bit socket	F 6.3
Torque range	100 - 500 cNm
Torque range	1 - 5 Nm
Reversible reading	cNm

Standard	DIN EN ISO 6789
Weight	436 g
Measurement process	Torque
Connection format	Bit holder 1/4 inch
Overall length L	200 mm
Trigger principle	mechanical short-travel release
Setting the trigger value	with adjustment scale
Feedback	triggering
Adjustable trigger value	adjustable
Calibration	O3
Direction of tightening	For right- and left-hand tightening
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Release signalling	akustisk
Release signalling	haptisk
Measurement technology	mechanical
Type of product	Torque screwdriver

Services

CalibrationTorque screwdrivers, clockwise / anti-clockwise maximum torque 0,04-20/2 N·m	020260 0,04-20/2
---	------------------