



## Double ratchet ring spanner for Torx® screws, Torx® profile: E20XE24



### Order data

Order number	619440 E20XE24
GTIN	4045197229991
Item class	62A

### Description

#### Version:

Drop forged. With particularly smooth-running ring ratchets. Extremely small working arc of 5°.

#### Material:

Chrome vanadium steel, chrome-plated.

overall length L: 230 mm

maximum ring  $\varnothing$  D1: 30.5 mm

maximum ring  $\varnothing$  D2: 32.5 mm

maximum ring height  $h_1$ : 10.4 mm

maximum ring height  $h_2$ : 11.2 mm

### Technical description

Torx® profile 1	E20
Torx® profile 2	E24
maximum ring $\varnothing$ D2	32.5 mm
maximum ring $\varnothing$ D1	30.5 mm
maximum ring height $h_2$	11.2 mm
maximum ring height $h_1$	10.4 mm
overall length L	230 mm
Drive profile	Socket for TORX® screws
No. of teeth	72
Working arc	5°

Material	Chrome vanadium steel
Surface	chrome-plated
Type of product	Spanner