



Torque screwdriver, Type: 9IP



Order data

Order number	659950 9IP
GTIN	4013288093400
Item class	63F

Description

Version:

Proven Kraftform handle, from 5 Nm with pistol grip. Every screwdriver is preset to the **correct torque for each size of screw**.

A sealing ring protects the mechanism in the handle from interference and inadvertent adjustment. Drive size and torque are stamped on the end of the handle.

When the set torque is reached the screwdriver triggers with clearly audible and perceptible signals. It is **not possible to tighten the screw any further**.

Size 2 – 4 for socket head screws.

Size TX6 – TX20 for screws with **Torx® profile**.

Size 6IP – 20IP for screws with **Torx Plus® profile**.

Application:

Ideal for fitting indexable inserts.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

set torque	1.4 Nm
Blade length	65 mm
Torque measuring accuracy	±10 %

set torque	140 cNm
Feedback	triggering
Setting the trigger value	preset
Trigger principle	mechanical slip clutch
Adjustable trigger value	non-adjustable
Connection format	fixed
Measurement process	Torque
Overall length L	175 mm
Reversible reading	cNm
Standard	DIN EN ISO 6789
Weight	117 g
Direction of tightening	Right-hand tightening
Data can be recorded	no
Measurement technology	mechanical
Release signalling	akustisk
Release signalling	haptisk
Drive profile	Screwdriver for TORX PLUS® screws
Manufacturer's designation	300 IP
Torque fixed setting	yes
Type of product	Torque screwdriver