



Double-ended open ring spanner, Width across flats: 11X13mm



Order data

| | |
|--------------|---------------|
| Order number | 619705 11X13 |
| GTIN | 4045197673367 |
| Item class | 62A |

Description

Version:

Drop forged; with reinforced ring, therefore exceptionally strong; jaw widths to exact tolerances. 10° angled heads.

With oval, easy grip shaft, very strong. Up to size 12×14 mm with hexagon ring - size 14×17 mm and above with bi-hexagon.

Standard:

DIN 3118 / ISO 3318

Material:

Chrome vanadium steel, chrome-plated.

Technical description

| | |
|------------------------------------|---------------------|
| maximum ring $\varnothing D_1$ max | 22.8 mm |
| Width across flats 1 | 11 mm |
| maximum ring height $h_{1\max}$ | 8.5 mm |
| maximum ring height $h_{2\max}$ | 10.5 mm |
| Spanner length L | 174 mm |
| Width across flats 2 | 13 mm |
| maximum ring $\varnothing D_2$ max | 25.3 mm |
| Width across flats | metric |
| Standard | DIN 3118 / ISO 3318 |
| Ring setting | 10 degrees |

| | |
|-----------------|-----------------------|
| Material | Chrome vanadium steel |
| Surface | chrome-plated |
| Type of product | Spanner |