



## Double ended ring spanner, straight, for Torx® screws, Torx® profile: E6XE8



### Order data

Order number	619400 E6XE8
GTIN	4018754022342
Item class	63A

### Description

#### Version:

Drop forged, straight design. Flat heads and thin rings for restricted places. Fluted shaft.

#### Material:

Chrome alloy steel, chrome-plated over nickel.

Spanner length L: 115.5 mm

maximum ring  $\varnothing D_1$  max: 9.6 mm

maximum ring  $\varnothing D_2$  max: 11.6 mm

maximum ring height  $h_{1\max}$ : 4.5 mm

maximum ring height  $h_{2\max}$ : 5.5 mm

### Technical description

Torx® profile 2	E8
maximum ring $\varnothing D_1$ max	9.6 mm
maximum ring $\varnothing D_2$ max	11.6 mm
maximum ring height $h_{2\max}$	5.5 mm
maximum ring height $h_{1\max}$	4.5 mm
Spanner length L	115.5 mm
Torx® profile 1	E6
Manufacturing process	drop forged
Material	Chrome alloy steel
Type of product	Spanner

