

Garant**NC spotting drill HSS-E-PM No. 112010 with plastic box 90°, Type: 6-12****Order data**

Order number	112105 6-12
GTIN	4045197893796
Item class	11A

Description**Version:**

NC spotting drill set in a plastic box.

High-performance NC spotting drill.

Tool material of sintered powder metallurgy **for applications** demanding high standards of tool life and centring accuracy. Very good wear resistance in stainless steels.

Precision centred ground point with thin chisel edge - gives easy spot drilling and high accuracy of the centre hole form. Very sturdy due to short flutes.

With drive flats to DIN 1835-B.**Content:**

4 NC spotting drill No. 112010.

Content:

1 each NC spotting drills: Size 6; 8; 10; 12.

Supplied with:

4-piece set of NC spotting drills in a plastic box.

Note:

Use speed for the actual hole Ø
(not necessarily the speed for the drill outer Ø).

Technical description

Nominal Ø D _c	6 mm
--------------------------	------

Nominal Ø D _c	8 mm
Nominal Ø D _c	10 mm
Nominal Ø D _c	12 mm
Tool material	HSS E PM
Standard	Manufacturer's standard
Type	N
Tolerance nominal Ø	h6
Point angle	90 degrees
Shank	DIN 1835 B to h6
Colour ring	without
Type of product	Spotting drill

Accessories

NC spotting drill HSS-E-PM90° N Ø DC h6 10 mm	112010 10
NC spotting drill HSS-E-PM90° N Ø DC h6 8 mm	112010 8
NC spotting drill HSS-E-PM90° N Ø DC h6 6 mm	112010 6
NC spotting drill HSS-E-PM90° N Ø DC h6 12 mm	112010 12