

KANON
Torque screwdriver with scale, maximum torque: 60cNm

Order data

Order number	659949 60
GTIN	4580125347533
Item class	66F

Description
Version:

Setting using a micrometer scale. Profiled light alloy handle.

Function:

When the set torque is reached the screwdriver triggers and signals clearly (audibly and perceptibly). It is then again immediately ready for use.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Ø	25 mm
Display	analogue
maximum torque	60 cNm
Scale graduation, 1 graduation =	0.5 cNm
Torque measuring accuracy	±6 %
Bit socket	F 6.3
Torque range	5 - 60 cNm
Torque range	0.05 - 0.6 Nm
Connection format	Bit holder 1/4 inch

Overall length L	110 mm
Feedback	triggering
Measurement process	Torque
Reversible reading	cNm
Adjustable trigger value	adjustable
Setting the trigger value	with adjustment scale
Standard	DIN EN ISO 6789
Trigger principle	mechanical short-travel release
Weight	99 g
Calibration	O3
Direction of tightening	For right- and left-hand tightening
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Release signalling	akustisk
Release signalling	haptisk
Measurement technology	mechanical
Type of product	Torque screwdriver

Services

CalibrationTorque screwdrivers, clockwise / anti-clockwise maximum torque 0,04-20/2 N·m	020260 0,04-20/2
---	------------------