

KANON
Torque screwdriver with scale, maximum torque: 120cNm

Order data

Order number	659949 120
GTIN	4580125347540
Item class	66F

Description
Version:

Setting using a micrometer scale. Profiled light alloy handle.

Function:

When the set torque is reached the screwdriver triggers and signals clearly (audibly and perceptibly). It is then again immediately ready for use.

Standard:

Geprüft nach DIN EN ISO 6789.

Note:

The guaranteed measuring accuracy of the torque is achieved only once the torque range has been calibrated to DIN EN ISO 6789.

Technical description

Display	analogue
Ø	30 mm
Scale graduation, 1 graduation =	1 cNm
maximum torque	120 cNm
Torque measuring accuracy	±6 %
Bit socket	F 6.3
Torque range	20 - 120 cNm
Torque range	0.2 - 1.2 Nm
Overall length L	157 mm

Weight	192 g
Adjustable trigger value	adjustable
Standard	DIN EN ISO 6789
Measurement process	Torque
Connection format	Bit holder 1/4 inch
Setting the trigger value	with adjustment scale
Reversible reading	cNm
Feedback	triggering
Trigger principle	mechanical short-travel release
Calibration	O3
Direction of tightening	For right- and left-hand tightening
Test certificate	Manufacturer's test certificate
Data can be recorded	no
Release signalling	akustisk
Release signalling	haptisk
Measurement technology	mechanical
Type of product	Torque screwdriver

Services

CalibrationTorque screwdrivers, clockwise / anti-clockwise maximum torque 0,04-20/2 N·m	020260 0,04-20/2
---	------------------