



Pneumatic-hydraulic pop rivet tool TAURUS®, Type: 1



Order data

Order number	770512 1
GTIN	4007081560009
Item class	74A

Description

Version:

Operating pressure 5 – 7 bar. Removable rivet pin capture box.

Advantage:

The **gripping jaw system** ensures very long tool life and a non-slip grip on the rivet spigot. Low compressed air consumption due to two-phase operation: for setting **and** for lifting away the broken-off tail. Very quick operating cycle.

Supplied with:

Assembly spanners 12 / 14 AF and 14 / 17 AF.

1 bottle hydraulic oil 100 ml and 1 oil refill container. Including nozzles 17/18, 17/20, 17/22.

Technical description

Air consumption per rivet	1 l
Weight	1.3 kg
for pop rivets in all materials up to	3.2 mm
maximum mandrel Ø	2.5 mm
Tool stroke	15 mm

for pop rivets steel / aluminium up to	4 mm
Hose connection	6 mm
Setting force at 5 bar	4200 N
Hose connection	1/4 in
Type of product	Pop riveter