



Double-ended open ring spanner, Width across flats: 14X17mm



Order data

Order number	619705 14X17
GTIN	4045197673381
Item class	62A

Description

Version:

Drop forged; with reinforced ring, therefore exceptionally strong; jaw widths to exact tolerances. 10° angled heads.

With oval, easy grip shaft, very strong. Up to size 12×14 mm with hexagon ring - size 14×17 mm and above with bi-hexagon.

Standard:

DIN 3118 / ISO 3318

Material:

Chrome vanadium steel, chrome-plated.

Technical description

Spanner length L	195 mm
Width across flats 1	14 mm
maximum ring $\varnothing D_1$ max	27.4 mm
maximum ring height $h_{2\max}$	12.5 mm
maximum ring $\varnothing D_2$ max	31.4 mm
Width across flats 2	17 mm
maximum ring height $h_{1\max}$	11 mm
Width across flats	metric
Standard	DIN 3118 / ISO 3318
Ring setting	10 degrees

Material	Chrome vanadium steel
Surface	chrome-plated
Type of product	Spanner