



## Pneumatic-hydraulic pop rivet tool TAURUS®, Type: 2



### Order data

Order number	770512 2
GTIN	4007081570008
Item class	74A

### Description

#### Version:

Operating pressure 5 – 7 bar. Removable rivet pin capture box.

#### Advantage:

The **gripping jaw system** ensures very long tool life and a non-slip grip on the rivet spigot. Low compressed air consumption due to two-phase operation: for setting **and** for lifting away the broken-off tail. Very quick operating cycle.

#### Supplied with:

Assembly spanners 12 / 14 AF and 14 / 17 AF.

1 bottle hydraulic oil 100 ml and 1 oil refill container. Including nozzles 17/24, 17/27, 17/29, 17/32.

### Technical description

for pop rivets steel / aluminium up to	6 mm
Setting force at 5 bar	9000 N
Tool stroke	18 mm
maximum mandrel Ø	3.2 mm
Hose connection	6 mm

Weight	1.6 kg
for pop rivets in all materials up to	5 mm
Air consumption per rivet	2.3 l
Hose connection	1/4 in
Type of product	Pop riveter