



Double ended ring spanner, straight, for Torx® screws, Torx® profile: E20XE24



Order data

Order number	619400 E20XE24
GTIN	4018754022373
Item class	63A

Description

Version:

Drop forged, straight design. Flat heads and thin rings for restricted places. Fluted shaft.

Material:

Chrome alloy steel, chrome-plated over nickel.

Spanner length L: 227 mm

maximum ring $\varnothing D_1$ max: 24.7 mm

maximum ring $\varnothing D_2$ max: 29.2 mm

maximum ring height $h_{1\max}$: 10.5 mm

maximum ring height $h_{2\max}$: 12.5 mm

Technical description

maximum ring height $h_{2\max}$	12.5 mm
maximum ring $\varnothing D_2$ max	29.2 mm
Spanner length L	227 mm
Torx® profile 1	E20
Torx® profile 2	E24
maximum ring height $h_{1\max}$	10.5 mm
maximum ring $\varnothing D_1$ max	24.7 mm
Manufacturing process	drop forged
Material	Chrome alloy steel
Type of product	Spanner

