



Precision circlip pliers, Type: A4



Order data

| | |
|--------------|---------------|
| Order number | 719890 A4 |
| GTIN | 4003773048756 |
| Item class | 73F |

Description

Version:

Forged grip and joint. Precision made tips of special steel, special precision profile and pressed into the body.

Pliers, chemically blacked. Plastic coated handles. Joint with **integral opening spring**. **Form A – straight jaws**.

Advantage:

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

Application:

For fitting and removing circlips.

Standard:

DIN 5254 A und B – für Außensicherungsringe.

Technical description

| | |
|-------------------------------------|-------------|
| for external circlips \varnothing | 85 - 140 mm |
| overall length | 320 mm |
| Shape | A |
| Tip \varnothing | 3.2 mm |
| Standard | DIN 5254 A |

| | |
|------------------------------------|----------------------|
| Use of circlip pliers | Outer ring, straight |
| Jaw shape | straight |
| Handle | plastic coated |
| Material | Special steel |
| Surface | chemically greyed |
| with over-expansion guard | no |
| Joint with integral opening spring | yes |
| Handle with self-grip mechanism | no |
| Exchangeable points | no |
| Type of product | Circlip Pliers |