



## Double-ended open ring spanner, Width across flats: 22X24mm



### Order data

Order number	619705 22X24
GTIN	4045197673411
Item class	62A

### Description

#### Version:

Drop forged; with reinforced ring, therefore exceptionally strong; jaw widths to exact tolerances. 10° angled heads.

With oval, easy grip shaft, very strong. Up to size 12×14 mm with hexagon ring - size 14×17 mm and above with bi-hexagon.

#### Standard:

**DIN 3118 / ISO 3318**

#### Material:

Chrome vanadium steel, chrome-plated.

### Technical description

Spanner length L	243 mm
Width across flats 2	24 mm
maximum ring $\varnothing D_1$ max	38.5 mm
maximum ring height $h_{1\text{ max}}$	15 mm
Width across flats 1	22 mm
maximum ring height $h_{2\text{ max}}$	16 mm
maximum ring $\varnothing D_2$ max	42 mm
Width across flats	metric
Standard	DIN 3118 / ISO 3318
Ring setting	10 degrees

Material	Chrome vanadium steel
Surface	chrome-plated
Type of product	Spanner