



Pneumatic-hydraulic pop riveter, Type: 2

Order data

Order number	770513 2
GTIN	4045197559975
Item class	72E

Description

Version:

Operating pressure 6 – 7 bar. Removable rivet pin capture box. Powerful and reliable pop riveter. Quick and reliable securing of pop rivets due to the powerful gripping system (grips the rivet pin without slipping). Variably adjustable suction to dispose the snapped rivet pins into the capture box.

Supplied with:

Nozzles (suitable for steel, stainless steel, aluminium, copper): 2.4 – 3.4 mm, 4 mm, 4.8 mm.

Nozzles (suitable for aluminium): 2.4 mm, 4.8 mm, 6 mm. 1 bottle hydraulic oil 50 ml.

Tool stroke: 21 mm

Setting force at 6 bar: 10500 N

Air consumption per rivet: 5.4 l

Hose connection: 8 mm

maximum mandrel Ø: 3.2 mm

for pop rivets in all materials up to: 5 mm

Technical description

Operating pressure	bar
Type of product	