



Precision circlip pliers, Type: A11



Order data

Order number	719890 A11
GTIN	4003773048824
Item class	73F

Description

Version:

Forged grip and joint. Precision made tips of special steel, special precision profile and pressed into the body.

Pliers, chemically blacked. Plastic coated handles. Joint with **integral opening spring. Form B –90° angled jaws.**

Advantage:

Pressed-in tips are highly durable even during continuous operation. Up to 10 times the working life of turned tips.

Application:

For fitting and removing circlips.

Standard:

DIN 5254 A und B – für Außensicherungsringe.

Use of circlip pliers: Outer ring, angled

overall length: 130 mm

for external circlips Ø: 10 - 25 mm

Tip Ø: 1.3 mm

Technical description

Shape	B
overall length	130 mm
for external circlips Ø	10 - 25 mm

Tip Ø	1.3 mm
Standard	DIN 5254 B
Use of circlip pliers	Outer ring, angled
Jaw shape	90° angled
Handle	plastic coated
Material	Special steel
Surface	chemically greyed
with over-expansion guard	no
Joint with integral opening spring	yes
Handle with self-grip mechanism	no
Exchangeable points	no
Type of product	Circlip Pliers