


**Bench grinding wheel D×T×H (mm), 150×20×32, Type: SC80****Order data**

Order number	596200 SC80
GTIN	9003171236330
Item class	53Y

Description**Version:**

High-quality long-lasting bench grinder wheels in ceramic bonding. Very low radial and axial run-out, maximum cutting speed 40 m/s. For **general use** on double-ended bench grinding machines for deburring, sharpening and resharpening tools.

Application:

For sharpening solid carbide and carbide-tipped tools as well as cast iron and tungsten components.

Specification:

Green **silicon carbide**, hardness grade J.

Supplied with:

Reducing ring set for the indicated bores.

Note:

For compact deburring wheels see No. 568725 ff.

Technical description

Grit designation	fine
Grit	80

Grinding medium code	SiC
maximum circumferential speed	40 m/s
Specification	Green silicon carbide, hardness grade J
Grinding media	Green Silicon Carbide
Grinding process	Bench grinder
Reducing ring inner Ø	25 mm
Reducing ring inner Ø	20 mm
Reducing ring inner Ø	16 mm
Shape	1
Disc Ø D	150 mm
Disc thickness T	20 mm
Product name attribute	150×20×32
Bore Ø H	32 mm
Type of product	Grinding wheel for off-hand grinders

Accessories

Reducing ring set for the natural bore of the grinding wheel 32 mm

596000 32