




## Diamond cup grinding wheel D×T×H (mm), 75×30×20, Type: D126



### Order data

Order number	597510 D126
GTIN	9003176796341
Item class	53Y

### Description

#### Version:

#### Cup grinding wheels and dished grinding wheels with diamond abrasive coating.

General-purpose grit for medium to fine surface quality and very good metal removal rates.

#### Specification: D126C75B DIAGO W-Carbide.

#### Application:

**For general use on all common tool grinding machines.** For grinding **carbide tools and short chipping non-ferrous materials.** Very well suited to dry grinding, but can also be used for wet grinding.

### Technical description

Grit	D126
Grinding medium code	D
Specification	D126C75B DIAGO W-Carbide
Grinding media	Diamond
Grinding process	Tool grinding
Shape	11V9
Disc Ø D	75 mm

Disc thickness T	30 mm
Product name attribute	75×30×20
Bore Ø H	20 mm
Abrasive coating width W end face	2 mm
Abrasive coating height X	10 mm
Type of product	Tapered cup grinding wheel

### User data

	Suitability	V <sub>c</sub>	ISO code
Carbide (HM)	suitable		
Plastic, GRP	suitable only under restricted conditions		
wet maximum	suitable only under restricted conditions		
dry	suitable		