

**CBN cup grinding wheel D×T×H (mm), 100×20×20, Type: B126****Order data**

Order number	597320 B126
GTIN	9003176366582
Item class	53Y

Description**Version:**

Tool grinding wheels with **CBN grit** in synthetic resin bonding for long service life and consistently high metal removal rates. The sandwich carrier body system of composite aluminium materials ensures high vibration damping and hence smooth grinding with consistent grinding results at high surface quality. For fine surface quality and good metal removal rates. **Specification: B126C75B AMIGO-HSS.**

Application:

For tool grinding on all common tool grinding machines. For grinding high alloy (HSS) tool steels and case-hardening steels, Stellite.

Technical description

Grit	B126
Grinding process	Tool grinding
Shape	12V9
Disc Ø D	100 mm

Disc thickness T	20 mm
Product name attribute	100×20×20
Bore Ø H	20 mm
Abrasive coating width W end face	2 mm
Abrasive coating height X	10 mm
Type of product	Tapered cup grinding wheel

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable only under restricted conditions		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
wet maximum	suitable only under restricted conditions		
dry	suitable		