

**Bench grinding wheel D×T×H (mm), 250×32×51, Type: EK80****Order data**

Order number	596510 EK80
GTIN	9003176640767
Item class	53Y

Description**Version:**

High-quality long-lasting bench grinder wheels in ceramic bonding. Very low radial and axial run-out, maximum cutting speed 40 m/s. For **general use** on double-ended bench grinding machines for deburring, sharpening and resharpening tools.

Application:

For hardened steels and HSS.

Specification:

White **electro-bonded aluminium oxide**, hardness grade M

Supplied with:

Reducing ring set for the indicated bores.

Note:

For compact deburring wheels see No. 568725 ff.

Technical description

Grit	80
Grit designation	fine

Grinding medium code	A
maximum circumferential speed	40 m/s
Specification	White electro-bonded aluminium oxide, hardness grade M
Grinding media	White electro-bonded Aluminium Oxide
Grinding process	Bench grinder
Reducing ring inner Ø	32 mm
Shape	1
Disc Ø D	250 mm
Disc thickness T	32 mm
Product name attribute	250×32×51
Bore Ø H	51 mm
Type of product	Grinding wheel for off-hand grinders

Accessories

Reducing ring set for the natural bore of the grinding wheel 51 mm	596000 51
--	-----------