

Garant
Hand reamer Configurable, uncoated, Nominal Ø DC: 10,5mm

Order data

| | |
|--------------|---------------|
| Order number | 160200 10,5 |
| GTIN | 4045197927026 |
| Item class | 10N |

Description
Version:

With **left-hand helix** 7 – 8° and long taper lead, more than 1/4 of the cutting length. An even number of teeth with irregular spacing for accurately round holes, free of chatter. The cylindrical ground chamfer on the plain cutting section smooths the hole and guides the reamer.

Hand reamers **finish ground to match your specifications.**

Application:

For through holes (not for blind holes). Also very suitable for interrupted holes.

Technical description

| | |
|---------------------------------------|------------------|
| Shank square <input type="checkbox"/> | 8 mm |
| Ø range | 10.101 - 10.6 mm |
| Flute length L _c | 66 mm |
| Number of cutting edges Z | 6 |
| Overall length L | 133 mm |
| Overhang L ₁ | 83 mm |
| Nominal Ø D _c | 10.5 mm |
| Coating | uncoated |
| Tool material | HSS |
| Standard | DIN 206 B |
| Helix angle | 7-8 degrees |
| Through-coolant | no |

| | |
|----------------------------------|-------------------|
| Application for type of drilling | for through holes |
| Colour ring | without |
| Type of product | Phillips bit |

User data

| | Suitability | V_c | ISO code |
|-------------------------------|---|----------------------|-----------------|
| Aluminium (short chipping) | suitable | | |
| Steel < 500 N/mm ² | suitable | | |
| Steel < 750 N/mm ² | suitable | | |
| Steel < 900 N/mm ² | suitable only under restricted conditions | | |
| Oil | suitable | | |
| dry | suitable only under restricted conditions | | |