

Garant**Heavy-duty side cutter, chrome-plated VDE insulated, overall length: 160mm****Order data**

Order number	723510 160
GTIN	4045197501608
Item class	71B

Description**Version:**

Heavy-duty head, induction hardened cutting edges (approx. 64 HRC), laid-on joint with no play. Jaws chrome-plated, handles with ergonomically optimised multi-component coverings with non-slip **Haptoprene** surface.

Insulated to DIN EN IEC 60900 / VDE 0682-201 for working at voltages up to 1000 V.

Standard:

DIN ISO 5749

Material:

Chrome vanadium steel, drop-forged and oil-hardened.

Technical description

Cutting capacity soft wire up to Ø	3.4 mm
Cutting capacity piano wire up to Ø	2 mm
overall length	160 mm
Cutting capacity hard wire up to Ø	2.5 mm
Standard	DIN EN IEC 60900 / VDE 0682-201
Standard	DIN ISO 5749
Handle	Multi-component covering with non-slip Haptoprene surface

Manufacturing process	Cutting edges induction hardened (approx. 64 HRC)
Material	Chromium vanadium steel
Surface	chrome-plated
Heavy-duty diagonal side cutter	no
with selectable return spring	no
Type of product	Cutting pliers