



Mechanic's side cutter chrome-plated with grips, overall length: 110mm



Order data

Order number	724200 110
GTIN	4003773029649
Item class	73F

Description

Version:

With slim head and induction hardened cutting edges. Cutter edge hardness approx. 63 HRC. Flush fitting joint with no play.

Jaws chrome-plated, handles with multi-component covering. With opening spring.

Standard:

DIN ISO 5749

Material:

Special tool steel, drop-forged, and oil-hardened.

Technical description

overall length	110 mm
Cutting capacity hard wire up to Ø	1.2 mm
Cutting capacity soft wire up to Ø	3 mm
with selectable return spring	no
with return spring	yes
Standard	DIN ISO 5749
Handle	Multi-component covering

Manufacturing process	Cutting edges induction hardened (approx. 63 HRC)
Material	Special tool steel, drop-forged and oil-hardened
Surface	chrome-plated
Type of product	Cutting pliers