



Mechanic's side cutter chrome-plated with grips, overall length: 125 mm



Order data

Order number	724200 125
GTIN	4003773005315
Item class	73F

Description

Version:

With slim head and induction hardened cutting edges. Cutter edge hardness approx. 63 HRC. Flush fitting joint with no play.

Jaws chrome-plated, handles with multi-component covering.

Standard:

DIN ISO 5749

Material:

Special tool steel, drop-forged, and oil-hardened.

Cutting capacity soft wire up to \varnothing : 2.5 mm

Cutting capacity hard wire up to \varnothing : 1 mm

Cutting capacity piano wire up to \varnothing : 0.6 mm

Technical description

Cutting capacity piano wire up to \varnothing	0.6 mm
overall length	125 mm
Cutting capacity hard wire up to \varnothing	1 mm
Cutting capacity soft wire up to \varnothing	2.5 mm
with selectable return spring	no
with return spring	no
Standard	DIN ISO 5749

Handle	Multi-component covering
Manufacturing process	Cutting edges induction hardened (approx. 63 HRC)
Material	Special tool steel, drop-forged and oil-hardened
Surface	chrome-plated
Type of product	Cutting pliers