


Garant
WN.G 080408, Grade: HU7305


Order data

Order number	252070 HU7305
GTIN	4045197927743
Item class	21G

Description

WN.G 080408 HU7305 Grade: HU7305
 Chip breaker: AM
 Tolerance: G
 Cutting depth a_p : 0.5 - 5 mm
 Feed f : 0.1 - 0.6 mm/rev.
 Cutting speed v_c main application: 400 - 600 m/min

Technical description

Chip breaker	AM
Cutting conditions	slightly interrupted
Main application	N
Cutting speed v_c main application	400 - 600 m/min
Cutting depth a_p	0.5 - 5 mm
Corner radius	0.8 mm
Feed f	0.1 - 0.6 mm/rev.

Grade	HU7305
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
Coating	uncoated
ISO code indexable insert	WNGG 080408
Number of changes/inserts	6
Tolerance	G
Type of product	Indexable insert for turning