



## Carbide-tipped hammer drill "MX4" SDS-plus, Øxoverall length: 12X160mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 789050 12X160 |
| GTIN         | 4002395366880 |
| Item class   | 76G           |

### Description

#### Version:

Drill head with square cross-section. Increased drilling speed due to 4-cutter head. Double the service life compared to 2 cutters. Large-volume 4-flute design. Sharper angled tip: more precision when drilling, no slipping along the surface, more aggressive in rebar and greater drilling speed.

PGM certified – verified precise and wall-plug-capable drill holes, both for chemical and for physical anchors. 4-edged, slotted, robust and **one-part soldered-on** carbide insert. New head design in combination with acute-angle tip permits optimum feed when encountering rebar.

#### Application:

For drilling concrete, natural stone, and masonry – with very high drilling comfort. Very smooth action, perfect for truly circular holes. 4-flute design for quick clearance of waste material, low vibration, and high stability. Less tiring for the operator and less load on the machine.

### Technical description

|                                  |                 |
|----------------------------------|-----------------|
| overall length                   | 160 mm          |
| Number of cutting edges Z        | 4               |
| Flute length                     | 100 mm          |
| Ø                                | 12 mm           |
| Tool material                    | Carbide         |
| Use with impact / without impact | Impact drilling |
| Shank                            | SDS Plus        |
| Type of product                  | Masonry drill   |

