


**Indexable insert for turning TNMG 160408, for medium machining****Order data**

Order number	251544 HU7305
GTIN	4045197927729
Item class	21G

Technical description

Cutting depth a_p	0.5 - 5 mm
Chip breaker	AM
Main application	N
Corner radius	0.8 mm
Cutting speed v_c main application	400 - 600 m/min
Type	HU7305
Cutting conditions	slightly interrupted
Feed f	0.1 - 0.6 mm/rev.
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
Coating	uncoated
ISO code indexable insert	TNGG 160408

Data sheet

Number of changes/inserts	6
Tolerance	G
Type of product	Indexable insert for turning