



Pneumatic impact wrench, Type: W2920



Order data

Order number	079171 W2920
GTIN	7322590051280
Item class	03R

Description

Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal Ø.
Powerful impact wrench.

Exhaust air passes through the handle, **reversible**.

- **Powerful impact hammer mechanism.**
- **Low weight combined with high performance.**
- **Composite body and handle with long working life.**
- **Ergonomic handle with good insulation.**
- **Reversal changeover by two buttons.**

Application:

Suitable for heavy-duty use.

Spare part:

Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

Length	218 mm
--------	--------

Reversible	yes
Operating noise	96 dB(A)
Torque range	300 - 1450 Nm
maximum speed	5500 min ⁻¹
Tool arbor size	3/4 in
maximum air consumption	1620 l/min
recommended hose size (internal Ø)	13 mm
maximum vibration to EN	10.2 m/s ²
Manufacturer's designation	W2920
Format	Pistol
Weight	3.2 kg
Height	206 mm
Tool arbor drive profile	□
Maximum screw Ø (8.8 - 12.9)	M30
Compressed air connection	3/8 in
Connection thread	BSP
Type of product	Screwdriver