


Garant
SNMG 150612, Grade: HB7120-1


Order data

Order number	251232 HB7120-1
GTIN	4045197928177
Item class	21G

Description

SNMG 150612 HB7120-1 Corner radius: 1.2 mm
 Grade: HB7120-1
 Chip breaker: VM
 Cutting depth a_p : 0.5 - 4 mm
 Feed f : 0.1 - 0.4 mm/rev.
 Cutting speed v_c main application: 80 - 260 m/min

Technical description

Cutting conditions	continuous
Corner radius	1.2 mm
Main application	M
Cutting depth a_p	0.5 - 4 mm
Grade	HB7120-1
Chip breaker	VM
Cutting speed v_c main application	80 - 260 m/min

Feed f	0.1 - 0.4 mm/rev.
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	SNMG 150612
Number of changes/inserts	8
Type of product	Indexable insert for turning