

Garant
GARANT Master Tap machine tap HSS-E-PM, ALTiX, UNF: 3/4-16

Order data

Order number	133410 3/4-16
GTIN	4045197901897
Item class	111

Description
Version:

GARANT Master Tap general-purpose tap, designed for use on a wide spectrum of materials with high process reliability.

- **HSS-E-PM tool material for maximum wear resistance.**
- **Reduced coefficient of friction due to the new high-performance coating.**
- **Special geometry for optimum swarf evacuation.**

Application:

For UNF unified fine threads ASME – B1.1.

Thread type: UNF

Tool material: HSS E PM

Standard: DIN 374

Threads per inch: 16

Thread Ø: 19.05 mm

Overall length L: 110 mm

Shank Ø D_s: 14 mm

Shank square □: 11 mm

Tapping hole Ø: 17.5 mm

Technical description

Number of cutting edges Z	3
Thread size	3/4-16 UNF
Threads per inch	16
Thread depth	57.15 mm

Standard	DIN 374
Number of clamping slots	3
Overall length L	110 mm
Thread pitch	1.587 mm
Thread type	UNF
Shank $\varnothing D_s$	14 mm
Shank square \square	11 mm
Thread \varnothing	19.05 mm
Tool material	HSS E PM
Tapping hole \varnothing	17.5 mm
Series	Master Tap
Coating	AlTiX
Flank angle	60°
Tolerance class	2BX
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Type of product	Tap

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	30 m/min	N
Aluminium (short chipping)	suitable	35 m/min	N
Alu > 10% Si	suitable	20 m/min	N

Steel < 500 N/mm ²	suitable	30 m/min	P
Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
Steel < 1400 N/mm ²	suitable	8 m/min	P
INOX < 900 N/mm ²	suitable	10 m/min	M
INOX > 900 N/mm ²	suitable	8 m/min	M
GG(G)	suitable	20 m/min	K
CuZn	suitable	20 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		