



Pneumatic impact wrench, Type: W2915



Order data

Order number	079171 W2915
GTIN	7322590051297
Item class	03R

Description

Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal Ø.
Powerful impact wrench.

Exhaust air passes through the handle, **reversible**.

- **Powerful impact hammer mechanism.**
- **Low weight combined with high performance.**
- **Composite body and handle with long working life.**
- **Ergonomic handle with good insulation.**
- **Reversal changeover by two buttons.**

Application:

Suitable for heavy-duty use.

Spare part:

Selected service kits: Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

Technical description

recommended hose size (internal Ø)	10 mm
------------------------------------	-------

Tool arbor size	1/2 in
Operating noise	96 dB(A)
Manufacturer's designation	W2915
Torque range	200 - 800 Nm
Height	186 mm
Maximum screw Ø (8.8 - 12.9)	M16
Format	Pistol
Tool arbor drive profile	□
maximum vibration to EN	7.5 m/s ²
Weight	2 kg
Length	185 mm
maximum speed	7700 min ⁻¹
Reversible	yes
maximum air consumption	1080 l/min
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Screwdriver