



## Centre cutter, overall length: 250mm



### Order data

Order number	725800 250
GTIN	4003773034070
Item class	73F

### Description

#### Version:

With particularly robust head and induction hardened cutting edges. Cutter edge hardness approx. 64 HRC. Jaws chemically blacked, polished head, plastic coated handles.

#### Advantage:

The force required is less than for side cutters with equal length handles.

#### Standard:

**DIN ISO 5743**

#### Material:

Chrome-vanadium high-performance steel, forged and multi-stage oil-hardened.

### Technical description

overall length	250 mm
Cutting capacity soft wire up to Ø	5 mm
Cutting capacity piano wire up to Ø	3.5 mm
Cutting capacity hard wire up to Ø	3.8 mm
Standard	DIN ISO 5743
Handle	plastic coated
Head	straight
Manufacturing process	Cutting edges additionally induction hardened approx. 64 HRC

Material	Chrome vanadium high-performance steel
Surface	Jaws chemically blacked, head bright polished
Type of product	Cutting pliers