

GARANT Master Tap machine tap HSS-E-PM, AITIX, UNF: 5/16-24



Order data

Order number	133410 5/16-24
GTIN	4045197901842
Item class	111

Description

Version:

GARANT Master Tap general-purpose tap, designed for use on a wide spectrum of materials with high process reliability.

- · HSS-E-PM tool material for maximum wear resistance.
- · Reduced coefficient of friction due to the new high-performance coating.
- · Special geometry for optimum swarf evacuation.

Application:

For UNF unified fine threads ASME – B1.1.

Thread type: UNF

Tool material: HSS E PM Standard: DIN 376 Threads per inch: 24 Thread Ø: 7.94 mm Overall length L: 90 mm Shank Ø D.: 8 mm

Shank square \square : 6.2 mm Tapping hole \varnothing : 6.9 mm

Technical description

Overall length L	90 mm
Standard	DIN 376
Shank Ø D _s	8 mm
Tool material	HSS E PM
Threads per inch	24

Number of cutting edges Z	3		
Number of clamping slots	3		
Tapping hole Ø	6.9 mm		
Thread Ø	7.94 mm		
Shank square □	6.2 mm		
Thread pitch	1.058 mm		
Thread type	UNF		
Thread size	5/16-24 UNF		
Thread depth	23.82 mm		
Series	Master Tap		
Coating	AlTiX		
Flank angle	60 °		
Tolerance class	2BX		
Taper lead form	В		
Shank	Plain shank with h9		
Through-coolant	no		
Application for type of drilling	up to 3×D for through holes		
Cutting direction	right-hand		
Type of threading tool	Machine tap for dynamic machining		
Colour ring	green		
Type of product	Тар		

User data

	Suitability	\mathbf{V}_{c}	ISO code
Alu plastics	suitable	30 m/min	N
Aluminium (short chipping)	suitable	35 m/min	N
Alu > 10% Si	suitable	20 m/min	N
Steel < 500 N/mm ²	suitable	30 m/min	Р

Steel < 750 N/mm ²	suitable	30 m/min	Р
Steel < 900 N/mm ²	suitable	25 m/min	Р
Steel < 1100 N/mm ²	suitable	12 m/min	Р
Steel < 1400 N/mm ²	suitable	8 m/min	Р
INOX < 900 N/mm ²	suitable	10 m/min	М
INOX > 900 N/mm ²	suitable	8 m/min	М
GG(G)	suitable	20 m/min	K
CuZn	suitable	20 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		