

**Garant**
**GARANT Master Tap machine tap HSS-E-PM, ALTiX, UNC: 10-24**

**Order data**

Order number	137870 10-24
GTIN	4045197901545
Item class	11I

**Description**
**Version:**

**GARANT Master Tap Universal tap**, designed for use in a wide spectrum of materials with high process reliability.

- **HSS-E-PM tool material for maximum wear resistance.**
- **Reduced coefficient of friction due to the new high-performance coating.**
- **Special geometry for optimum swarf evacuation.**

**Application:**

**For UNC uniform coarse threads** ASME – B1.1.

Thread type: UNC

Tool material: HSS E PM

Standard: DIN 371

Threads per inch: 24

Thread Ø: 4.83 mm

Overall length L: 70 mm

Shank Ø D<sub>s</sub>: 6 mm

Shank square □: 4.9 mm

Tapping hole Ø: 3.9 mm

**Technical description**

Tapping hole Ø	3.9 mm
Shank square □	4.9 mm
Thread Ø	4.83 mm
Thread depth	12 mm
Number of clamping slots	2

Thread pitch	1.058 mm
Thread size	10-24 UNC
Shank $\varnothing D_s$	6 mm
Tool material	HSS E PM
Overall length L	70 mm
Number of cutting edges Z	2
Standard	DIN 371
Threads per inch	24
Thread type	UNC
Series	Master Tap
Coating	AlTiX
Flank angle	60°
Tolerance class	2BX
Taper lead form	C
Helix angle	40°
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2.5×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Type of product	Tap

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable	30 m/min	N
Aluminium (short chipping)	suitable	35 m/min	N
Alu > 10% Si	suitable	20 m/min	N

Steel < 500 N/mm <sup>2</sup>	suitable	30 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	30 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	25 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	12 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	8 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	10 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	8 m/min	M
GG(G)	suitable	20 m/min	K
CuZn	suitable	20 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		