

## ROLLER

### One-hand pipe bender set in a sheet steel case



#### Order data

Order number	821200
GTIN	4044942026359
Item class	84C

#### Description

##### Version:

Robust bending drive of cast aluminium with mechanical rack advance (quick advance and quick withdraw), a universal slide carrier, and bending formers of glass fibre-reinforced polyamide. Bending angles of up to 180° achievable.

##### Application:

For bending soft uncased copper pipes, sheathed steel pipes for the Mapress Carbon Steel push-fitting system, precision mild steel pipes to DIN2391 - 2394, plain or sheathed and connecting pipes for the push-fitting system.

##### Content:

Bending drive: 1 pc.

Universal slide: 1 pc.

1 each bending segment for pipe external Ø: Size 12; 15; 18; 22 mm

Bending radius (centre of pipe): Size 36; 55; 72; 86 mm

#### Technical description

Bending radius (centre of pipe)	36 mm
Bending radius (centre of pipe)	55 mm
Bending radius (centre of pipe)	72 mm
Bending radius (centre of pipe)	86 mm
Number of bending drives	1

Number of bending segments	4
maximum bending angle	180 degrees
Material of bending drive	Aluminium die-casting
Type of product	Bending machine