

► LINDSTRÖM

## Electronics oblique end cutter with long jaws, SFW, overall length: 118 mm



### Order data

Order number	726860 118
GTIN	7314150051397
Item class	73M

### Description

#### Version:

Slim style with precision ground induction hardened jaw edges (63 - 65 HRC). Black surface to reduce reflections. Yellow plastic grips of conductive material with return spring. **Suitable for ESDs.** Adjustable precision screw joint for minimal friction and optimum axial alignment of the cutters.

#### Material:

High performance steel alloy, drop forged, burnished.

Cutting chamfer: very fine bevel

Head length  $L_1$ : 18 mm

Head width: 10 mm

Cutting capacity copper wire up to  $\varnothing$ : 0.2 - 1 mm

### Technical description

Head width	10 mm
Cutting capacity copper wire up to $\varnothing$	0.2 - 1 mm
Head length $L_1$	18 mm
overall length	118 mm
electrical insulation	EGB/ESD
Cutting chamfer	very fine bevel
Joint	adjustable

Type of jaws	long, hollowed
Handle	Plastic grips
Manufacturing process	Cutting edges induction hardened (63 – 65 HRC)
Material	High-performance steel alloy
Surface	black burnished
Product name attribute	SFW
with return spring	yes